

LED Spotlights



HIGHLIGHTS :

WATTS



NA

EQ. WATTS



NA

LUMINOUS



NA

BEAM ANGLE



NA

SKU Code	: 3579
Base / holder	: GU10
Voltage	: AC 90-230V,50/60HZ
IP Rating Protection Class	: IP20
Body type	: ALUMINUM
Dimmable	: No
EAN code	: 3800157606981
Packing details	: 50
Unit cbm	: 0.00118

PRODUCT FEATURES

- No Lead or Mercury content hence Environment friendly
- Totally flexible, Compact & Adjustable design
- Provides Uniform Radiance & Enhances appeal of any environment
- No Ultraviolet or Infrared Rays
- Enhances measurable levels of performance as compared to older versions of high wattage halogen & HID light sources in retail & Commercial Lighting applications Showrooms, Super Markets, Shops, hotels, Living Rooms, Museums etc

[CLICK HERE FOR OTHER RELATED CERTIFICATES](#)