

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0391001810](#)  
**Status:** **Active**  
**Overview:** Eurostyle™ Two-Screw Barrier Strips  
**Description:** 8.00mm Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 10 Circuits

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Terminal Blocks
Series	39100
Application	Wire-to-Wire
Component Type	One Piece
Overview	<a href="#">Eurostyle™ Two-Screw Barrier Strips</a>
Product Name	Eurostyle™ Two Screw
Type	Barrier Strip
UPC	78172545128

**Physical**

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel
Material - Resin	Nylon
Net Weight	26.880/g
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	8.00mm
Pitch - Termination Interface	8.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	12, 14, 16, 18, 20, 22

**Electrical**


Current - Maximum per Contact	20.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	M800-01-10-5-M1
--------------------	-----------------

**Reference - Drawing Numbers**

Sales Drawing	SD-39100-011
---------------	--------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

**Search Parts in this Series**

[39100 Series](#)