

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300150098](#)
Status: **Active**
Overview: Brad® Mini-Change® Connectors
Description: Mini-Change® C-Size Receptacle, 19 Poles, 1-1/8" - 16 UN-2A Threads, Female (Straight) to Leads, 0.30m (11.81") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	130015
Comments	C-Size (1-1/8" - 16 UN-2A)
IP Rating	IP67
Overview	Brad® Mini-Change® Connectors
Product Name	Mini-Change®
Type	Single Ended (pigtail)
UPC	78678841463

Physical

Coupling Type	External Thread
Gender	Female
Keyway	Single
Length	0.30m
Material - Component	Gray Anodized Aluminum
Mounting Thread Size	PG16
Orientation	Straight
Panel Mount	Back, Front
Poles	19
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	18, 22
Wire/Cable Type	N/A

Electrical


Current - Maximum per Contact	2.0A
Voltage - Maximum	300V AC/DC

Material Info

Old Part Number	3R3N30E80C300
-----------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-130015-008
---------------	---------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

[130015 Series](#)