

HL Stick – The new expert for fine working

TECHNICAL DATA	
Product code:	004019
Dimensions (h x w x d):	780 x 760 x 2350 mm
Voltage:	230 v 50 Hz
Output:	350 W
Temperature:	400 °C, 500 °C with reduction nozzle
Air Flow:	100 l/min
Switches:	1 (On/Off)
Specials:	Incl. LED / Stable hanging
Length Power Cord:	2.20 m
Weight:	572 g
Motor:	Brush motor
Heating element:	Ceramic
Accessories included:	7mm reduction nozzle, reduction nozzle with protection reflector, 10mm and 40mm reflector nozzles

Available April 2012



Working punctual and precise with hot air!

This small ergonomically shaped hot air tool enables work in confined places as well