

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934456112](#)
Status: **Active**
Overview: [ML-XT™ Sealed Connection System](#)
Description: ML-XT™ Sealed 12 Circuit Plug Housing, Pre-Assembled with Small Rear Seal and Cover, Keying Option A, Grey

Documents:

[Drawing \(PDF\)](#) [Packaging Specification 934430002 \(PDF\)](#)
[Product Specification 934430010 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification 934430010 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	93445
Application	Power, Signal, Wire-to-Wire
Overview	ML-XT™ Sealed Connection System
Product Name	ML-XT™
UPC	889056308250

Physical

Circuits (maximum)	12
Color - Resin	Grey
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	15.700/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	934430010
Packaging Specification	934430002
Product Specification	934430010
Sales Drawing	934430060



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93445](#) Series

Mates With

ML-XT™ Sealed 12 Circuit Receptacle Housing [93444-6112](#)

Use With

ML-XT™ Female (Socket) Terminal [84525-0009](#) (Nickel), ML-XT™ Female (Socket) Terminal [84525-0032](#) (Selective Gold), ML-XT™ 12 Circuit Plug Wedgelock [93448](#) , ML-XT™ Blind Cavity Plug [93494-1000](#)