


Heat Shrinkable Tubing adhesive lined - 1.2 m lengths

- TA42 - thin wall, 4:1 shrink ratio



Heat Shrinkable Tubing 4:1 with adhesive

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Length (L)	Colour	Shrink Ratio	Article-No.
TA42-4/1	4.0	1.0	1.00	1.2 m	Black (BK)	4:1	318-40400
TA42-8/2	8.0	2.0	1.20	1.2 m	Black (BK)	4:1	318-40800
TA42-12/3	12.0	3.0	1.40	1.2 m	Black (BK)	4:1	318-41200
TA42-16/4	16.0	4.0	1.80	1.2 m	Black (BK)	4:1	318-41600
TA42-24/6	24.0	6.0	2.25	1.2 m	Black (BK)	4:1	318-42400
TA42-32/8	32.0	8.0	2.55	1.2 m	Black (BK)	4:1	318-43200
TA42-52/13	52.0	13.0	2.55	1.2 m	Black (BK)	4:1	318-45200

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



Please note! Not all products listed on this page may have this approval.
For product specific approvals please refer to the Appendix.

Heat Shrinkable Tubing up to 4:1 - 1 m lengths

- MA47 - medium wall adhesive lined
- MU47 - medium wall unlined

Insulation and Protection of low voltage cable joints and terminations above and below ground.

Features and Benefits

- Medium walled tubing with robust insulation characteristics
- Shrink tubing for above and underground cable applications
- Protects cable joints and terminations in low voltage applications
- Coated inside with thermoplastic adhesive
- Protects against humidity and other environmental impacts after shrinking



MA47 and MU47 medium wall tubing - lined and unlined.

Cut lengths available on request. Please contact us!

MATERIAL	Polyolefin, cross-linked (PO-X)
Shrink Ratio	up to 4:1
Operating Temperature	-55 °C to +110 °C
Minimum Shrink Temperature	+120 °C
Softening Point Adhesive	+85 °C
Longitudinal change after shrinkage	-10% max.
Dielectric Strength	20 kV/mm
Flammability	not flame retarded
Insulation Class	A (VDE 0530)





Heat Shrinkable Tubing up to 4:1 - 1 m lengths

- MA47 - medium wall adhesive lined



Heat Shrinkable Tubing 4:1 with adhesive

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Length (L)	Colour	Article-No.
MA47-12/3	12.0	3.0	2.00	1.0 m	Black (BK)	323-20120
MA47-19/6	19.0	6.0	2.50	1.0 m	Black (BK)	323-20190
MA47-30/8	30.0	8.0	2.50	1.0 m	Black (BK)	323-20300
MA47-40/12	40.0	12.0	2.50	1.0 m	Black (BK)	323-20400
MA47-50/16	50.0	16.0	2.70	1.0 m	Black (BK)	323-20500
MA47-63/19	63.0	19.0	2.80	1.0 m	Black (BK)	323-20630
MA47-75/22	75.0	22.0	3.00	1.0 m	Black (BK)	323-20750
MA47-95/30	95.0	30.0	3.00	1.0 m	Black (BK)	323-20950
MA47-115/34	115.0	34.0	3.00	1.0 m	Black (BK)	323-21150
MA47-140/42	140.0	42.0	3.00	1.0 m	Black (BK)	323-21400

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.

- MU47 - medium wall unlined



Heat Shrinkable Tubing 4:1

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Length (L)	Colour	Article-No.
MU47-12/3	12.0	3.0	2.00	1.0 m	Black (BK)	323-10120
MU47-19/6	19.0	6.0	2.20	1.0 m	Black (BK)	323-10190
MU47-30/8	30.0	8.0	2.50	1.0 m	Black (BK)	323-10300
MU47-40/12	40.0	12.0	2.50	1.0 m	Black (BK)	323-10400
MU47-50/16	50.0	16.0	2.70	1.0 m	Black (BK)	323-10500
MU47-63/19	63.0	19.0	2.80	1.0 m	Black (BK)	323-10630
MU47-75/22	75.0	22.0	3.00	1.0 m	Black (BK)	323-10750
MU47-95/30	95.0	30.0	3.00	1.0 m	Black (BK)	323-10950
MU47 115/34	115.0	34.0	3.00	1.0 m	Black (BK)	323-11150
MU47-140/42	140.0	42.0	3.00	1.0 m	Black (BK)	323-11400

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.