



Non-Metallic Sheathed Cable Conduit Fittings

T&B Catalog Number:

3305M

UPC Number:

78621080555

Status:

Active

Description:

1 1/4 in. Insulated Two Screw Connector, Malleable Iron-Electro Zinc Plated.

Features

Rounded cable grip and smooth bushing protect the cable sheath and wire insulation. Since saddle is threaded, screws do not travel or extend beyond the connector body as it is clamped to the cable. An extra lip on the saddle closes the unused part of the connector opening.

Application

To connect non-metallic sheathed cable and flexible cord to a box or an enclosure.

General

Material	Malleable Iron
Finish	Electro Zinc Plated

Dimension Information

Dimension A (inches)	1 15/16
Dimension B (inches)	2 7/32
Dimension C (inches)	1 5/8
Knockout Size (inches)	1 1/4
Cable Opening-Minimum (inches)	0.850
Cable Opening-Maximum (inches)	1.320

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	5
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	27.4 lbs. per 100

Notes

- *Note U.L. listed and CSA certified for the following pairs of (2) NM and NMC cable; (2) 2#8, 2#6, 2#4, 3#8.
- **Note U.L. listed and CSA certified for the following Service Entrance Cables; GND, 2#1/0 + #2 GND, 2#2/0 + #1 GND.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 17583

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com