





Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection	Housing	Front Cap/Face	Power LED	Output LED	Mating Cord, Cable Length/Jacket	Wiring Diagram #	Wiring Diagrams
10-65 VDC	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	6	<b>Diagram 1</b> 
	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	1	<b>Diagram 2</b> 
10-30 VDC	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	1	<b>Diagram 2</b> 
	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	1	<b>Diagram 2</b> 
10-30 VDC	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	2	<b>Diagram 3</b> 
	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	2	<b>Diagram 3</b> 
20-250 VAC 10-65 VDC	20	≤100	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	3	<b>Diagram 4</b> 
	20	≤100	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	3	<b>Diagram 4</b> 
10-30 VDC	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	RKK 4T-*	4	<b>Diagram 5</b> 
	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	RKK 4T-*	4	<b>Diagram 5</b> 
10-30 VDC	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	RKK 4T-*	5	<b>Diagram 6</b> 
	2000	≤200	-25 to +70	IP 67	PBT	PBT	N/A	YE	RKK 4T-*	5	<b>Diagram 6</b> 

Rectangular

For material descriptions see page M22.