

SC-1080P-DWID CCTV Dome Camera



FEATURES

Image Sensor	1/2.7" Pixart 2.1MP CMOS Sensor
Resolution	1080P
Signal System	PAL / NTSC
Minimum Illumination	0.01 Lux/F1.2
S/N Ratio	More than 40B
Synchronous System	Internal
IR Distance	20 Meters (with 14μ x 18PCS Infrared LED)
IR Power On	Photodiode AUTO Control
Video Output	AHD,TVI,CVBS,CVI
Power/Current	DC12V(+/-10%)/500mA
Lens	Board Len 3.6mm
Weather Proof	IP 65
Dimension (mm)	90.5(W) x 80(H) x 80(D)
Weight (g)	300
Operating Conditions	-10~+50°C RH95% MAX

