

Aluminum Electrolytic, 105C, ELG, 120 uF, 20%, 450 V, -25/+105C



| Dimensions | |
|------------|---------------|
| D | 25mm +/-1mm |
| L | 35mm +/-2mm |
| S | 10mm +/-0.5mm |
| LL | 5.8mm +/-1mm |
| F | 2mm +/-0.1mm |

| Packaging Specifications | |
|--------------------------|------|
| Packaging: | Bulk |

| General Information | |
|---------------------|--------------------------------|
| Dielectric: | Aluminum Electrolytic |
| Series: | ELG |
| Description: | Snap-In, Aluminum Electrolytic |
| RoHS: | Yes |
| Lead: | 2 Pin |

| Specifications | |
|------------------------|--------------------------|
| Capacitance: | 120 uF |
| Capacitance Tolerance: | 20% |
| Voltage DC: | 450 VDC, 500 VDC (Surge) |
| Temperature Range: | -25/+105C |
| Rated Temperature: | 105C |
| Life: | 2000 Hrs |
| Dissipation Factor: | 20% 120Hz 20C |
| Resistance: | 532 mOhms (20kHz) |
| Current: | 700 mAmps (120Hz) |
| Leakage: | 1100 uAmps (5min 20C) |