

Film, Metallized Paper, Safety, P295, 560 pF, 20%, 1,500 V, 500 V, 115C, Lead Spacing = 15mm



**Dimensions**

L	18mm MAX
H	12.5mm MAX
T	5.5mm MAX
S	15mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

**Packaging Specifications**

Packaging:	Bulk
Packaging Quantity:	1100

**General Information**

Dielectric:	Metallized Paper
Style:	Radial
Series:	P295
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL, CQC
Miscellaneous:	SRF= 59 MHz

**Specifications**

Capacitance:	560 pF
Capacitance Tolerance:	20%
Voltage DC:	1500 VDC
Voltage AC:	500 VAC
Temperature Range:	-40/+115C
Rated Temperature:	115C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dVdt:	2,000 V
Safety Class:	Y1