

Film, Metallized Polypropylene, Safety, R47_X1, 0.022 uF, 10%, 1,000 V, 440 V, 110C, Lead Spacing = 15mm



Dimensions

L	18mm +0.3mm
H	12mm +0.1mm
T	6mm +0.2mm
S	15mm +/-0.4mm
LL	25mm +2/-1mm
F	0.6mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	900

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R47_X1
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	AEC-Q200, ENEC, UL, cUL
AEC-Q200:	Yes

Specifications

Capacitance:	0.022 uF
Capacitance Tolerance:	10%
Voltage DC:	1000 VDC
Voltage AC:	440 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	0.1% 1kHz
Insulation Resistance:	100 GOhms
Max dVdt:	600 V
Safety Class:	X1