

Film, Metallized Polypropylene, Safety, R47_X1, 0.47 uF, 10%, 1,000 V, 440 V, 110C, Lead Spacing = 27.5mm



General Information	
Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R47_X1
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL

Dimensions	
L	32mm +0.3mm
H	22mm +0.1mm
T	13mm +0.2mm
S	27.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	0.47 uF
Capacitance Tolerance:	10%
Voltage DC:	1000 VDC
Voltage AC:	440 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	0.1% 1kHz
Insulation Resistance:	63.8298 GOhms
Max dVdt:	225 V
Safety Class:	X1

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	288