

**KEMET Part Number: R75QI23305000J**  
(75QI23305000J)

Film, Metallized Polypropylene, Commercial Grade, R75, 0.033 uF, 5%, 1,000 V, 85C, Lead Spacing = 15mm



General Information	
Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R75
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Above 85C DC And AC Voltage Derating Is 1.25%/C

Dimensions	
L	18mm +0.3mm
H	12mm +0.1mm
T	6mm +0.2mm
S	15mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	900

Specifications	
Capacitance:	0.033 uF
Capacitance Tolerance:	5%
Voltage DC:	1000 VDC
Voltage AC:	250 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz
Insulation Resistance:	100 GOhms
Max dVdt:	2,000 V
Inductance:	10 nH