

KEMET Part Number: SU9H-02080
(UALSU9H0208000)



Commercial Grade, SU-9V/9H, 8000 uH

General Information

Style:	Through-Hole Choke
Series:	SU-9V/9H
Description:	Common Mode Filter
RoHS:	Yes
Miscellaneous:	Inductance Measurement Condition: 1kHz 1V KC530

Specifications

Inductance:	8000 uH
Rated Temperature:	120C
Current:	0.2 mAmps (Irms, 40C Rise By Self Heating)
Voltage AC:	250 VAC
DC Resistance:	6 Ohms
Insulation Resistance:	100 MOhms

Dimensions

L	17mm MAX
T	15.5mm MAX
H	12.5mm MIN
S	7mm +/-0.5mm
S1	8mm +/-0.5mm
LL	4mm MIN
F	0.6mm NOM

Packaging Specifications

Weight:	3.2 g
----------------	-------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2017 IntelliData.net