

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0151660127](#)  
**Status:** **Active**  
**Overview:** Premo-Flex™ Cable Jumpers  
**Description:** 0.50mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 12 Circuits, 0.152m Cable Length, Cable Thickness 0.12mm, Tin (Sn) Plating

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	15166
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	<a href="#">Premo-Flex™ Cable Jumpers</a>
Product Name	Premo-Flex™FFC Jumper
UPC	884982846197

**Physical**

Cable Length	0.152m
Circuits (Loaded)	12
Circuits (maximum)	12
Net Weight	1.000/g
Packaging Type	Bag
Pitch - Termination Interface	0.50mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-15166-001
---------------	--------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

**China RoHS**

Green Image  
Not Relevant

**Search Parts in this Series**

[15166 Series](#)

**Use With**

<a href="http://www.molex.com/product/ffcfcpc\_th.html">Molex FFC – FPC connector</a>. Be sure to match like plating