

Datasheet for part number DBMMN13W3PN

Our Catalog Part Number: DBMMN-13W3P-N

Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D

| Designed Detections | |
|---------------------------------|---|
| Product Datasheet | |
| General | Combo D Series: D-Subminiature offering mixed layouts |
| Wire Gauge Range AWG | AWG 8-26 |
| Mating Cycles | 500 |
| Contact Arrangement | 13W3 (10 contacts size 20, 3 empty size 8 cavities) |
| Dielectric Withstanding Voltage | 500 VAC at sea level |
| Current Rating Signal Contacts | 7.5 max |
| Contact Resistance | 10 milli Ohm max |
| Operating Temperature | -55°/+150° |
| Salt Spray Test | 48 hours {96 Hrs for Stainless Steel} |
| Shell Material | steel |
| Shell Finish | Yellow chromate over zinc |
| Insulator Material | Thermoplastic, type PCT UL 94V-0 |
| Insulator Color | black |
| Gender | Pin |
| Contact Type | Straight PCB US footprint |
| Contact Material | copper alloy |
| Contact Finish | gold over nickel (Performance Class 1) |
| Mounting Method | .300? (7.6mm) Standoff, 4-40 Screwlock, Boardlock |