

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0982660106**
Status: **Active**
Overview: Premo-Flex™ Cable Jumpers
Description: 0.50mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 10 Circuits, 0.152m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

Documents:

[Drawing \(PDF\)](#)
[Product Specification PS-98266-001 \(PDF\)](#)
[Packaging Specification PK-98266-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	98266
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ Cable Jumpers
Product Name	Premo-Flex™ FFC Jumper
UPC	756054767399

Physical

Cable Length	0.152m
Circuits (Loaded)	10
Net Weight	0.499/g
Packaging Type	Bag
Pitch - Termination Interface	0.50mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98266-001
Product Specification	PS-98266-001
Sales Drawing	SD-98266-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

98266 Series

Use With

Molex FFC – FPC connector. Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION