



Datasheet for part number DBMM9W4SA101

Our Catalog Part Number: DBMM-9W4S-A101
Our Global Manufacturing Part Number: 051523-0156
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D

Product Datasheet	
General	Combo D Series: D-Subminiature offering mixed layouts
Wire Gauge Range AWG	AWG 8-26
Contact Arrangement	9W4 (5 contacts size 20, 4 empty size 8 cavities)
Dielectric Withstanding Voltage	500 VAC at sea level
Current Rating Signal Contacts	7.5 max
Operating Temperature	-55°/+150°
Salt Spray Test	48 hours (96 Hrs for Stainless Steel)
Shell Material	Carbon Steel
Shell Finish	Cadmium plating
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Socket
Contacts	delivery without size 8 contacts, please order separately
Mounting Method	.120" (3,05mm) Through Hole