



Datasheet for part number DBMMY9W4PNK87

| |
|---|
| Our Catalog Part Number: DBMMY-9W4P-N-K87 |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D |

| Product Datasheet | |
|---------------------------------|---|
| General | Combo D Series: D-Subminiature offering mixed layouts |
| Wire Gauge Range AWG | AWG 8-26 |
| Contact Arrangement | 9W4 (5 contacts size 20, 4 empty size 8 cavities) |
| Dielectric Withstanding Voltage | 500 VAC at sea level |
| Current Rating Signal Contacts | 7.5 max |
| Operating Temperature | -55°/+150° |
| Salt Spray Test | 48 hours (96 Hrs for Stainless Steel) |
| Shell Material | steel |
| Shell Finish | pure tin over nickel |
| Insulator Material | Thermoplastic, type PCT UL 94V-0 |
| Insulator Color | black |
| Gender | Pin |
| Contacts | delivery without size 8 contacts, please order separately |
| Mounting Method | Dual Float Mount |