

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300061438](#)  
**Status:** **Active**  
**Overview:** Brad® Mini-Change® Connectors  
**Description:** Mini-Change® A-Size Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 16 AWG, PVC Cable, 1.83m (6.0') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Cordsets  
 Series [130006](#)  
 Connector End A Mini-Change®  
 Connector End B Pigtail  
 IP Rating IP67  
 Overview [Brad® Mini-Change® Connectors](#)  
 Product Name Mini-Change®  
 Protocol N/A  
 Region America  
 Type Single Ended  
 UPC 78678840152

**Physical**

Cable Diameter 12.70mm (.500")  
 Cable Length 1.83m (6.0')  
 Color - Cable Jacket Yellow  
 Coupling Style Threaded  
 Gender Male-Pigtail  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body PVC  
 Material - Contact Brass  
 Material - Coupling Nut Black Epoxy Coated Zinc  
 Material - Plating Mating Gold  
 Orientation Straight  
 Poles 5  
 Temperature Range - Operating -20°C to +105°C  
 Wire Size AWG 16  
 Wire/Cable Type ST00W

**Electrical**


Current - Maximum per Contact 8.0A  
 Voltage - Maximum 600V

**Material Info**

Old Part Number 105002A01F060

**Reference - Drawing Numbers**

Sales Drawing SD-130006-005



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

**Search Parts in this Series**

[130006 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**