

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0732511851](#)
Status: **Active**
Overview: Precision Compression-Mount Microwave Test Connectors
Description: 50 Ohms, Precision Test Connector, Optimized SMA Jack, Two Hole Flange with 2 Screws 4.76mm, 0-80 Threads

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	RF/Coax Connectors
Series	73251
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	Optimized SMA
Style	PCB
UPC	822350628181
Wire/Cable Type	N/A

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	1.990/g
Orientation	Straight
PCB Mounting	Surface Mount
PCB Thickness - Recommended	3.05mm
Packaging Type	Bag
Panel Mount	Yes
Panel Mount Method	Flange
Reverse Polar	No

Electrical

Impedance	50#
-----------	-----

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-73251-185
---------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

[73251](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION