

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348978240](#)
Status: **Active**
Overview: [Mini50™ Connection Systems](#)
Description: Mini50™ Unsealed Right Angle SMT Header, Dual Row, 24 Circuit, Polarization Option A, Black, Tape and Reel

Documents:

[3D Model](#) [Product Specification PS-34791-020 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family PCB Headers
 Series [34897](#)
 Application Power, Signal, Wire-to-Board
 Overview [Mini50™ Connection Systems](#)
 Product Name Mini50™
 UPC 887191459332

Physical

Breakaway No
 Circuits (Loaded) 24
 Circuits (maximum) 24
 Color - Resin Black
 First Mate / Last Break No
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part Yes
 Lock to Mating Part Yes
 Material - Metal Brass
 Material - Plating Mating Tin over Nickel
 Material - Plating Termination Tin over Nickel
 Material - Resin High Temperature Thermoplastic
 Net Weight 3.649/g
 Number of Rows 2
 Orientation Right Angle
 PCB Locator Yes
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 2.00mm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 500V DC

Material Info

Reference - Drawing Numbers

Product Specification PS-34791-020
 Sales Drawing GU5T-14F262-DA, SD-34897-001

EU ELV
Compliant

EU RoHS
Compliant

REACH SVHC
Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free
Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Relevant
ELV Compliant

Search Parts in this Series

[34897 Series](#)

Mates With

[34824 Mini50™ Unsealed Dual Row Receptacle](#)