

## General Information

Extended Product Type:	RB121G-24VUC
Product ID:	1SNA645005R0700
EAN:	4013614507762
Catalog Description:	RB121G-24VUC Interface relay R600 1c/o,A1-A2=24VAC/DC,250V/3mA-6A
Long Description:	Screw relay RB121A 24vac/dc : 24vac-dc input / 1SPDT 1 mA upto 6A with led

## Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

## Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85364900
EAN:	4013614507762

## Dimensions

Product Net Height:	67.5 mm
Product Net Depth:	70 mm
Product Net Weight:	0.02 kg
Product Net Width:	6 mm

## Container Information

Package Level 1 Width:	73 mm
Package Level 1 Height:	71 mm
Package Level 1 Length:	80 mm
Package Level 1 Gross Weight:	0.23 kg
Package Level 1 EAN:	3472596450052
Package Level 1 Units:	10 piece

## Technical

Sub-Function:	Relay with built in LED
Output:	1 c/o (SPDT) contact
Output Signal:	5 ... 250 V AC / 1 mA ... 6 A
Rated Control Supply Voltage (U <sub>s</sub> ):	24 V AC/DC
Terminal Type:	Screw Terminals
Function:	Boxed interface relay R600

## Environmental

RoHS Status:	Following EU Directive 2011/65/EC
--------------	-----------------------------------

## Certificates and Declarations (Document Number)

Instructions and Manuals:	1SVC645000M9000
CB Certificate:	CB_DK-53188-UL
CSA Certificate:	CSA_254821
cUR Certificate:	cUR_E352056
Data Sheet, Technical Information:	1SVC117001D0200
Declaration of Conformity - CE:	1SVD982016-0000
EAC Certificate:	EAC_RU_C-FR.ME77.B.01634
LR Certificate:	LR_16_20068
RoHS Information:	1SVD982016-4400
UR Certificate:	UR_E352056

## Classifications

ETIM 4:	EC001437 - Switching relay
ETIM 5:	EC001437 - Switching relay
ETIM 6:	EC001437 - Switching relay
eClass:	7.0 27371601
UNSPSC:	39121500
Object Classification Code:	K

