

General Information

Extended Product Type:	RB122G-48-60VUC
Product ID:	1SNA645040R1500
EAN:	4013614508004
Catalog Description:	RB122G-48-60VUC Interface relay R600 2c/o,A1-A2=48-60VAC/DC,250V/1mA-8A
Long Description:	Screw relay RB122A 48-60vac/dc : 48-60vac-dc input / 1DPDT 1 mA upto 8A with led

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

Ordering

Minimum Order Quantity:	5 piece
Customs Tariff Number:	85364900
EAN:	4013614508004

Dimensions

Product Net Height:	67.5 mm
Product Net Depth:	70 mm
Product Net Weight:	0.04 kg
Product Net Width:	12 mm

Container Information

Package Level 1 Width:	73 mm
Package Level 1 Height:	71 mm
Package Level 1 Length:	80 mm
Package Level 1 Gross Weight:	0.24 kg
Package Level 1 EAN:	3472596450403
Package Level 1 Units:	5 piece

Technical

Sub-Function:	Relay with built in LED
Output:	2 c/o (SPDT) contacts
Output Signal:	5 ... 250 V AC / DC / 1 mA ... 8 A
Rated Control Supply Voltage (U _s):	48 ... 60 V AC/DC
Terminal Type:	Screw Terminals
Function:	Boxed interface relay R600

Environmental

RoHS Status:	Following EU Directive 2011/65/EC
--------------	-----------------------------------

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SVC645000M9000
CB Certificate:	CB_DK-53188-UL
CSA Certificate:	CSA_254821
cUR Certificate:	cUR_E352056
Data Sheet, Technical Information:	1SVC117001D0200
Declaration of Conformity - CE:	1SVD982016-0000
EAC Certificate:	EAC_RU_C-FR.ME77.B.01634
LR Certificate:	LR_16_20068
RoHS Information:	1SVD982016-4400
UR Certificate:	UR_E352056

Classifications

ETIM 4:	EC001437 - Switching relay
ETIM 5:	EC001437 - Switching relay
ETIM 6:	EC001437 - Switching relay
eClass:	7.0 27371601
UNSPSC:	39121500
Object Classification Code:	K

