

## General Information

Extended Product Type:	JB5-4
Product ID:	1SNK905304R0000
EAN:	3472599097575
Catalog Description:	JB5-4 Jumper Bar - Orange
Long Description:	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

## Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010
Color:	Orange

## Dimensions

Product Net Height:	18.6 mm
Product Net Length:	26.8 mm
Product Net Depth:	26.8 mm
Product Net Weight:	2.7 g
Product Net Width:	5.2 mm

## Technical

Spacing:	5.2 mm
Function:	Jumper Bars
Rated Current ( $I_n$ ):	Main Circuit 32 A
Rated Short-time Withstand Current ( $I_{cw}$ ):	for 1 s 480 A
Rated Voltage ( $U_r$ ):	1000 V
Rated Impulse Withstand Voltage ( $U_{imp}$ ):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZDK2.5-22 ZDP2.5-11 ZDP2.5-22 ZDP2.5-D1 ZDP2.5-D2 ZDS4-22 ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-CH-4P ZK2.5-D1 ZK2.5-D1-PE ZK2.5-D2 ZK2.5-D2-PE ZK2.5-D-CH ZK2.5-PE ZK2.5-PE-3P ZK2.5-PE-4P ZK2.5-S ZK2.5-S-4P ZK2.5-SP ZK2.5-SP-4P ZP2.5 ZP2.5-3P ZP2.5-4P ZP2.5-D1 ZP2.5-D2 ZP2.5-PE ZP2.5-PE-3P

ZP2.5-PE-4P  
ZS4  
ZS4-D1  
ZS4-D2  
ZS4-D2-S  
ZS4-D2-S-T  
ZS4-D-CH  
ZS4-T3

## Technical UL/CSA

**Flammability According to UL94:** V0  
**Maximum Operating Voltage UL/CSA:** Main Circuit 600 V

## Environmental

**Resistance to Vibrations acc. to IEC 60068-2-6:** Compliant  
**RoHS Status:** Following EU Directive 2002/95/EC August 18, 2005 and amendment  
**Ambient Air Temperature:** Operation -55 ... +110 °C  
Storage -55 ... +110 °C

## Certificates and Declarations (Document Number)

**Instructions and Manuals:** 1SNK160027C0201  
**ATEX Certificate:** 1SND162004A1706  
**CB Certificate:** 1SND161017A0202  
**Data Sheet, Technical Information:** 1SNK160027D0201  
**RoHS Information:** 1SND230499F0202

## Classifications

**E-nummer:** 2925368  
**ETIM 4:** EC000489 - Cross-connector for terminal block  
**ETIM 5:** EC000489 - Cross-connector for terminal block  
**ETIM 6:** EC000489 - Cross-connector for terminal block  
**Object Classification Code:** X

## Container Information

**Package Level 1 Width:** 50 mm  
**Package Level 1 Length:** 117 mm  
**Package Level 1 Height:** 50 mm  
**Package Level 1 Gross Weight:** 0.135 kg  
**Package Level 1 EAN:** 3472599097575  
**Package Level 2 Units:** 1500 piece  
**Package Level 3 Units:** 144000 piece  
**Package Level 1 Units:** 50 piece

