



Datasheet for part number DCMMG13H6SJA197

|   |
|---|
| Our Catalog Part Number: DCMMG-13H6S-J-A197                               |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D |

| Product Datasheet               |   |
|---------------------------------|---|
| General                         | Combo D Series: D-Subminiature offering mixed layouts       |
| Wire Gauge Range AWG            | AWG 8-26  |
| Mating Cycles                   | 500   |
| Contact Arrangement             | 13H6 (7 contacts size 20, 6 contacts size 8)                |
| Dielectric Withstanding Voltage | 500 VAC at sea level  |
| Current Rating Signal Contacts  | 7.5 max   |
| Current Rating Size 8 Contacts  | 40 A max  |
| Contact Resistance              | 10 milli Ohm max  |
| Operating Temperature           | -55°/+150°  |
| Salt Spray Test                 | 48 hours {96 Hrs for Stainless Steel}                       |
| Shell Material                  | steel   |
| Shell Finish                    | pure tin over nickel  |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                            |
| Insulator Color                 | black   |
| Gender                          | Socket  |
| Contact Type                    | Right angle US footprint                                    |
| Contact Material                | copper alloy  |
| Contact Finish                  | gold over nickel (Performance Class 1)                      |
| Mounting Method                 | 90° Metal Bracket, 4-40 Fastener, 4-40 Screwlock, Boardlock |