

### General Information

Extended Product Type:	OHBS3RH
Product ID:	1SCA105237R1001
EAN:	6417019411811
Catalog Description:	OHBS3RH Handle
Long Description:	Selector type handle. Screw mounting, hole distance 36 mm. Indication I-O and ON-OFF. No separate shaft needed. Padlockable with one padlock, IP 54, NEMA 1, black, OT16...40FT

### Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

### Ordering

EAN:	6417019411811
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85381000

### Dimensions

Product Net Width:	48 mm
Product Net Height:	48 mm
Product Net Depth:	36 mm
Product Net Weight:	0.1 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	48 mm
Package Level 1 Height:	36 mm
Package Level 1 Length:	48 mm
Package Level 1 Gross Weight:	0.1 kg
Package Level 1 EAN:	6417019411811

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

### Additional Information

Color:	Black
Degree of Protection:	IP54
Handle Type:	Selector
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	10 piece
Product Main Type:	OHBS3RH
Product Name:	Handle
Product Type:	OHBS
Suitable For:	OT16 ... 63FT
Suitable for Product Class:	Switch disconnectors

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
RoHS Information:	1SCC390005D0202

### Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

