



Datasheet for part number DAMZ7H2PNK127

| |
|---------------------------------------------------------------------------|
| Our Catalog Part Number: DAMZ-7H2P-N-K127 |
| Our Global Manufacturing Part Number: 053512-1742 |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D |

| Product Datasheet | |
|---------------------------------|-------------------------------------------------------|
| General | Combo D Series: D-Subminiature offering mixed layouts |
| Wire Gauge Range AWG | AWG 8-26 |
| Mating Cycles | 50 |
| Contact Arrangement | 7H2 (5 contacts size 20, 2 contacts size 8) |
| Dielectric Withstanding Voltage | 500 VAC at sea level |
| Current Rating Signal Contacts | 7.5 max |
| Current Rating Size 8 Contacts | 40 A max |
| Contact Resistance | 10 milli Ohm max |
| Operating Temperature | -55°/+125° |
| Salt Spray Test | 20 hours |
| Shell Material | steel |
| Shell Finish | Tin over nickel plating |
| Insulator Material | Thermoplastic, type PCT UL 94V-0 |
| Insulator Color | black |
| Gender | Pin |
| Contact Type | Straight PCB US footprint |
| Contact Material | copper alloy |
| Contact Finish | 30 Micro-inch gold |
| Mounting Method | .300" (7.6mm) 4-40 Standoff, Boardlock |