



Datasheet for part number KJL6T21B41PN

Our Catalog Part Number: KJL6T21B41PN
Our Global Manufacturing Part Number: 111081-0009
Brand: Cannon Product Category: Circular Product Line: 38999 Series I, II, and III Series: KJ

Product Datasheet	
SERIES	MIL - DTL - 38999 Series I
STYLE	Straight plug
CLASS	Environment resistant (without rear accessory)
SHELL SIZE	21
SHELL MATERIAL	Corrosion resistant shells of aluminum alloy
INSULATOR MATERIAL	High grade plastic
GROMMET AND SEAL MATERIAL	Silicone base elastomer
PLATING	Olive drab cadmium over electroless nickel plate
ARRANGEMENT	21-41
NUMBER OF CONTACTS	41 contacts size 20
GENDER	Pin
CONTACT TYPE	Rear release crimp snap-in contacts
CONTACT MATERIAL	Copper Alloy, gold plate
POLARIZATION	95°
LOW PROFILE / LIGHT WEIGHT	no
SCOOP PROOF	yes
COUPLING SYSTEM	Bayonet
ELECTROLYTIC EROSION	no
DURABILITY (CYCLES)	500
HIGH IMPACT SHOCK	yes
EXTERNAL BENDING MOMENT (Size 25)	650 in/lbs
RANDOM VIBRATION "J"	Ambient
SINE VIBRATION	30 G, Ambient
SAND, DUST, ICE	yes
TEMPERATURE RANGE	65°C (85°F) to + 175°C (+347°F)
CORROSION RESISTANT	500 hours
TEST SERVICE RATING (MATED)	Sea Level = 1800 50000 ft. = 1000 70000 ft. = 1000 100000 ft. = 1000
TEST SERVICE RATING (UNMATED)	Sea Level = 1800 50000 ft. = 600 70000 ft. = 400 100000 ft. = 200
OPERATING VOLTAGE	Vrms = 600 Vdc = 850