

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530144](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Safeway® User Attachable GFCI In-Line, Manual Reset, Non-Corded, 20A, 120V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E66308

General

Product Family Power Distribution
 Series [130153](#)
 Enclosure Rating NEMA 4
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
 Product Literature Order No 987650-7737, 987651-0452
 Product Name Safeway®
 Receptacle Type N/A
 Type GFCI Commercial Duty, Single Phase
 UPC 78678828436
 Woodhead Yes

Physical

Cord Diameter N/A
 Cord Grip Body Size Internal Double C-Clamp
 Cord Length N/A
 Feed-Thru Yes
 Flip Lid No
 Material - Housing N/A
 Net Weight 249.475/g
 Number of Receptacles 1
 Packaging Type Bag

Electrical

Cord Type N/A
 Current - Maximum per Contact 20.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration N/A
 Voltage - Maximum 120V AC

Material Info

Engineering Number 20054



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed
 ELV Not Relevant
 RoHS Phthalates Not Reviewed

Search Parts in this Series

[130153 Series](#)