

Desktop 2-Post Rack *HDR Series*

195 lbs Weight Capacity



The Hammond Desktop Rack (HDR) Series features a small form factor perfect for small projects. Available in 8U, 12U and 16U options, this rack series is ideal for smaller IT, Security and AV applications.

Features

- Base and panel constructed in 16-gauge steel.
- Includes two (2) 12-gauge steel 19 inch EIA-310-D compliant mounting rails.
 - Rails are 10-32 tapped rails with rack space indicators.
 - Rails are angled 10-degrees when rack is assembled.
 - Starter pack of 25 rack screws included.
- Available in 8U, 12U and 16U rack spacing.
- Side of rails include multiple tie points for cable management.
- Finished in smooth black powder paint.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Tested to nearly double the suggested load rating of 195 lbs (89 kg).
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Universal Rack Shelf
- 10-32 Mounting Hardware
- Rack Panels
- Two Post Mounting Adjustable Shelf
- Outlet Strips

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Base Depth		Height	Width
HDR8UBK	16.00	20.00	11.50	8U	14.00	19.00
HDR12UBK	23.00	20.00	11.50	12U	21.00	19.00
HDR16UBK	30.00	20.00	16.00	16U	28.00	19.00

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, Two-Post Rack** *Data subject to change without notice*

