

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002098104**
Status: **Active**
Overview: Standard .093" Pin and Socket Connectors
Description: 2.36mm Diameter, Standard .093" Pin and Socket Crimp Grounding Terminal, Series 1973, Male, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-1190-003 \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	<u>1973</u>
Application	Power
Comments	Grounding Pin
Crimp Quality Equipment	Yes
Overview	<u>Standard .093" Pin and Socket Connectors</u>
Packaging Alternative	<u>02-09-8103 (Reel)</u>
Product Name	Standard .093"
UPC	800754230476

Physical


Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.343/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22
Wire Size mm ²	N/A

Material Info

Engineering Number 1973-A(P901)L

Reference - Drawing Numbers

Packaging Specification	PK-1190-003
Product Specification	PS-02-09
Sales Drawing	SD-1973-*



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

1973 Series

Use With

1619 Plug or Receptacle Housing, 1545 Plug or Receptacle Housing, 1396 Plug or Receptacle Housing, 1490 Plug or Receptacle Housing, 2629 Plug or Receptacle Crimp Housings, 1261 Plug or Receptacle Housing, 1292 Plug or Recept