

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0520440845](#)
Status: **Active**
Overview: FFC-FPC (Through-Hole)
Description: FFC/FPC Connector, Non-ZIF, Right-Angle, Top Contact Style Receptacle, 8 Circuits

Documents:

[3D Model](#) [Product Specification PS-52044-002-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family FFC/FPC Connectors
 Series 52044
 Overview FFC-FPC (Through-Hole)
 Product Name Non-ZIF
 UPC 800753572607

Physical

Circuits (Loaded) 8
 Contact Position Top
 Entry Angle 90° Angle
 Flammability 94V-0
 Mated Height 5.10mm
 Net Weight 785.300/mg
 Number of Rows 1
 Orientation Right Angle
 PC Tail Length 3.50mm
 PCB Retention None
 Packaging Type Tray
 Pitch - Mating Interface 1.25mm
 Polarized to PCB Yes
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40°C to +85°C
 Termination Interface: Style Through Hole
 Wire/Cable Type FFC/FPC


Electrical

Current - Maximum per Contact 0.5A, 1.0A
 Voltage - Maximum 200V

Material Info

Reference - Drawing Numbers

Product Specification PS-52044-002-001
 Sales Drawing SD-52044-**45



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

52044 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION