

### An introduction to Rotacraft

Rotacraft offers an excellent range of precision tool kits - 12 volt, 230 volt and Cordless, suitable for the beginner, the enthusiast and the professional user. The tools are supported by a wide range of attachments and accessories ideal for modelling, electronics, general household DIY, craft work, antique repair & restoration, engraving, jewellery making plus a variety of other precision tasks. (Rotacraft is available with UK & EU mains plugs)

### 12 Volt Power Tools

These tools are powered by permanent magnet direct current motors that operate from transformers with outputs up to 18 volts. The combination of a DC motor and a transformer has a number of advantages:

- Low voltage for extra safety
- Smaller tools as the motors are smaller and lighter
- Ample power for small, detailed tasks

### 12 VOLT SETS

Ideal for smaller detailed tasks where close up control is important



#### Mini Rotary Tool kit

This is an excellent starter kit

Features:

- Single Speed 12 volt compact rotary tool with plug-in transformer
- 18,000 rpm • 2.4m of cables (tool & transformer cables combined)
- 44 various accessories incl.collets 1, 2.35, 3, 3.2mm
- Attractive aluminium carry and storage case

RC12



#### Mini Variable Speed Rotary Tool kit

Compact variable speed for a wider range of uses  
Features:

- Speeds 0-18,000 rpm
- Plug-in transformer
- 3 grip positions - palm, pistol & pencil
- 50 various accessories incl. collets 1, 2.35, 3, 3.2mm
- Attractive aluminium carry and storage case

RC12VS



## 12 Volt Sets (Continued)



### RC18 Variable Speed Rotary tool kit

Pen style for extra close-up control

#### Features:

- Pen-like 12-18v Rotary tool + transformer
- In-built speed control 8000-18000 rpm
- 4m of cables (tool & transformer cables combined)
- 60 various accessories Inc. collets 1, 2.35, 3, 3.2mm
- Attractive aluminium carry and storage case

RC18



## Cordless Tool Set

### Cordless Power Tool

The cordless rotary tool is a must for every tool box, giving unrestricted mobility and versatility. Rotacraft offers a 9.6v variable speed version to cater for the lighter as well as heavier user. With up to 60 minutes usage between charges, the cordless rotary tool is excellent for field use or where mains power is inaccessible. The compact size means that work can be carried out in tight spaces where larger tools will not reach.

*Ideal for tasks where freedom and flexibility are required*



### Variable Speed Cordless rotary tool

Extra power, variable speed and LED light for close-up work

#### Features:

- 9.6v, variable speed - 6000 - 25000 rpm
- 2 grip positions - pen & pistol
- 3 hour charge - up to 60 minutes usage
- 100 various accessories including collets 1, 2.35, 3, 3.2mm
- Additional LED spotlight feature for lighting dark areas
- Attractive aluminium carry and storage case

RC09



### 9.6V Ni - Cd re-chargeable battery

- Spare battery for RC09 Cordless tool

RC09/B