

KEMET Part Number: PME264NC5330MR30
(P264CP333M660A)

Film, Metallized Paper, Safety, PME264/P264, 0.033 uF, 20%, 1,500 V, 660 V, 85C, Lead Spacing = 20.3mm



Dimensions

Dimension	Value
L	24mm MAX
H	16.5mm MAX
T	11.3mm MAX
S	20.3mm +/-0.5mm
LL	30mm +5mm
F	0.8mm NOM

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	150

General Information

Dielectric:	Metallized Paper
Style:	Radial
Series:	PME264/P264
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL
Construction:	Molded

Specifications

Capacitance:	0.033 uF
Capacitance Tolerance:	20%
Voltage DC:	1500 VDC
Voltage AC:	660 VAC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dVdt:	1,000 V
Safety Class:	X2