



## Platinum Resistance Pt100 4 wire class B Resistance Thermometer with Compact KNS Head



- Pt100 probe with compact KNS terminal head
- Class B, 4 wire connection
- Various probe available lengths
- 6.0mm diameter in 316 stainless steel
- IP67 aluminium alloy weatherproof connection head
- Sensor temperature rating -100°C to +450°C
- Conforms to IEC 751

### Specifications

Sensor type:	Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 wire
Construction:	6.0mm diameter stem in 316 stainless steel
Termination:	IP67 KNS connection head
Probe temperature range:	-100°C to +450°C (connection head @ 170°C)
Cable entry:	M16 x 1.5mm

Probe DiaØ	Probe length	order code
6.0mm	100mm	XF-955-FAR
6.0mm	150mm	XF-953-FAR
6.0mm	200mm	XF-956-FAR
6.0mm	250mm	XF-957-FAR
6.0mm	300mm	XF-958-FAR

### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com