

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0510040300](#)
Status: **Active**
Overview: MicroBlade™ Connection System
Description: 2.00mm Pitch MicroBlade™ Wire-to-Board Housing, Friction Lock, 5.80mm Height, 3 Circuits

Documents:

[3D Model](#) [Product Specification PS-51004-002-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series 51004
 Application Signal, Wire-to-Board
 Overview MicroBlade™ Connection System
 Product Name MicroBlade™
 UPC 800753575929

Physical

Circuits (maximum) 3
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Compliant No
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 96.500/mg
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.00mm
 Stackable No
 Temperature Range - Operating -20°C to +85°C


Electrical

Current - Maximum per Contact 2.0A

Material Info

Reference - Drawing Numbers

Product Specification PS-51004-002-001
 Sales Drawing SD-51004-**00



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

51004 Series

Mates With

53014 , 53015 , 53025 MicroBlade™ Headers

Use With

50011 Crimp Terminal