



GREENLEE®
A Textron Company

There With You™
faster • safer • easier®

**All 3 Tips
Included in New
540-20P Kit**
(Whisk, "J" Hook and Bullet)

GLO STIX & FISH STIX

FIBERGLASS RODS
FOR PULLING WIRES

3/16" & 5/32"
DIA. GLO STIX

1/4" DIA
FISH STIX



NEW

540-8M shown on 18" Tool Bag
(Bag not included in 540-8M kit)



Expanded Glo Stix/Fish Stix Kit Offering

Greenlee has expanded its kit offering with a new compact 540-8M Mini Glo Stix Kit with (5) 20" long 3/16" Glo Stix sections, bullet and "J" hook nose tips. Greenlee's second new kit offering is the 540-20P Professional Installer's Kit featuring 20' reach and including: (3) 4' long 1/4" Fish Stix, (2) 2' long 3/16" Glo Stix and (1) 4' long 5/32" Glo Stix along with whisk, "J" hook and bullet nose tips.

Greenlee's Glo Stix are manufactured from luminescent 3/16" or 5/32" diameter fiberglass rods that glow in the dark. The Glo Stix make installation of electrical, voice, data, video, and security wires easier in dark spaces. The 3/16" and 5/32" diameter are more flexible for going around corners in tight places.

Greenlee Fish Stix are manufactured from green 1/4" diameter fiberglass rods. The 1/4" diameter Fish Stix are relatively stiff to span longer unsupported distances.

All of the rods have sturdy steel threaded connectors on each end. The threads are the same on all rods, so different diameter rod sections can be combined easily for specific situations. Each Fish Stix and Glo Stix kit includes a bullet nose tip for pushing through insulated walls, under floors or above ceilings, and includes a hook tip for hooking wires and pulling them into position. Check out Greenlee's full line of Glo Stix and Fish Stix - made for the job at hand.

Features

GLO STIX

- Glo Stix are made from luminescent fiberglass for better visibility in dark locations.
- The 3/16" diameter Glo Stix are more flexible (4-1/4" minimum bend radius) for reaching shorter unsupported distances and use around corners.
- The 5/32" Glo Stix are the most flexible (3-1/2" minimum bend radius) and are best for working around corners, in walls, etc.
- Clear non-metallic storage tubes keep the Glo Stix "charged".
- Sturdy steel threaded connectors allow interchangeability of different size Fish Stix and Glo Stix (The 540-6 is a single stick with a fixed bullet nose on both ends.)
- 200 lbs. maximum pulling strength.
- Optional whisk nose tip available for fishing over obstacles, guiding extended Stix sideways by rolling, and providing a tip that can be snagged from the opposite direction with another Fish Stix or Glo Stix (using the hook nose). Included in new 540-20P kit.

FISH STIX

- Fish Stix are made from green fiberglass.
- The 1/4" diameter Fish Stix are relatively stiff (6-1/2" minimum bend radius) and are best suited for reaching long unsupported distances.
- Sturdy steel threaded connectors allow interchangeability of different size Fish Stix and Glo Stix.
- 200 lbs. maximum pulling strength.
- Optional whisk nose tip available for fishing over obstacles, guiding extended Stix sideways by rolling, and providing a tip that can be snagged from the opposite direction with another Fish Stix or Glo Stix (using the hook nose). Included in new 540-20P kit.



Specifications

	NEW			NEW			
	540-6	540-8M	540-12	540-15	540-18	540-20P	540-24
Overall Length	6' (1.8 m)	8' (2.4 m)	12' (2.7 m)	15' (4.6 m)	18' (5.5 m)	20' (6.1 m)	24' (7.3 m)
Number of Sections	1	5	3	3	3	6	5
Section Length	6' (1.8 m)	20" (.5 m)	4' (1.2 m)	5' (1.5 m)	6' (1.8 m)	†	3- 6', 2- 3'*
Diameter	5/32"	3/16"	1/4"	3/16"	5/32"	†	1/4"
Material Type	Glo Stix	Glo Stix	Fish Stix	Glo Stix	Glo Stix	†	Fish Stix

*One 3' section is a Glo Stix. †540-20P includes: (3)-1/4" x 4' Fish Stix sections, (2)-3/16" x 2' Glo Stix Sections & (1)-5/32" x 4' Glo Stix Section.

Order Information

CAT NO.	UPC NO.	DESCRIPTION	QTY.
540-6	86795	Single 5/32" x 6' long Glo Stix with fixed bullet nose tip at both ends	1
NEW 540-8M	12918	3/16" x 8' long Glo Stix Kit with bullet & "J" hook nose tips	1
540-12	10504	1/4" x 12' long Fish Stix Kit with bullet & "J" hook nose tips	1
540-15	11422	3/16" x 15' long Glo Stix Kit with bullet & "J" hook nose tips	1
540-18	86796	5/32" x 18' long Glo Stix Kit with bullet & "J" hook nose tips	1
NEW 540-20P	12919	Professional Installers Kit: Includes (3)-1/4" x 4' Fish Stix sections, (2)-3/16" x 2' Glo Stix Sections & (1)-5/32" x 4' Glo Stix Section, (1) whisk, (1) "J" hook, (1) bullet nose	1
540-24	10506	1/4" x 24' long Fish Stix Kit with bullet & "J" hook nose tips	1
10497	10497	A Hook Nose Tip	1
10498	10498	A Bullet Nose Tip	1
11426	11426	A Whisk Nose Tip	1
11427	11427	R 3/16" x 5' Glo Stix Section	1
11583	11583	R 1/4" x 4' Fish Stix Section	1
11584	11584	R 1/4" x 6' Fish Stix Section	1
11585	11585	R 3/16" x 3' Glo Stix Section	1
NEW 12920	12920	R 3/16" x 20" Glo Stix Section	1
NEW 12922	12922	R 5/32" x 4' Glo Stix Section	1
89803	89803	R 5/32" x 6' Glo Stix Section	1

DISTRIBUTED BY:

R = REPLACEMENT PART **A** = ACCESSORY



USA Tel: 800.435.0786
Fax: 800.451.2692

Canada Tel: 800.435.0786
Fax: 800.524.2893

International Tel: +1.815.397.7070
Fax: +1.815.397.9247