

VLSH1S5R

TeSys VLS - rec. rot. handle - screwfixing - red - shaft 5 mm - 65x65 mm

Product availability : Stock - Normally stocked in distribution facility



Main

Range	TeSys
Device short name	VLSH
Product or component type	Rotary handle
Range compatibility	TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks, with diameter 4...8 mm
Marking	0 - 1

Complementary

Fixing mode	By 4 screws
Tightening torque	20.35 lbf.in (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.56 in (65 mm)
Width	2.56 in (65 mm)
Depth	1.81 in (46 mm)
Product weight	0.16 lb(US) (0.073 kg)

Environment

IP degree of protection	IP65
NEMA degree of protection	NEMA 1 NEMA 4 NEMA 4X

Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
----------	---------------------------------------

Discount Schedule	CP1
GTIN	00785901575894
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14000000000000001
Returnability	Y
Country of origin	IT