

# Product data sheet

## Characteristics

# VLSH3S7BD

TeSys VLS - pistol handle - screwfix. - black - shaft 7 mm - 65x65 mm - defeat.

Product availability : Stock - Normally stocked in distribution facility



### Main

Range	TeSys
Device short name	VLSH
Product or component type	Rotary handle
Range compatibility	TeSys VARIO LS VLS3P
Handle colour	Black
Handle front plate colour	Grey
Rotary handle padlocking	1 to 3 padlocks, with diameter 4...8 mm
Marking	0 - 1

### Complementary

Fixing mode	By 4 screws
Tightening torque	13.27 lbf.in (1.5 N.m)
Base dimension	75 x 75 mm
Height	2.95 in (75 mm)
Width	2.95 in (75 mm)
Depth	2.72 in (69 mm)
Product weight	0.03 lb(US) (0.014 kg)

### Environment

IP degree of protection	IP66
NEMA degree of protection	NEMA 1 NEMA 4 NEMA 4X

### Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
----------	---------------------------------------

Discount Schedule	CP1
GTIN	00785901577690
Nbr. of units in pkg.	1
Package weight(Lbs)	0.41999999999999998
Returnability	Y
Country of origin	IT