

816 RA Ratchet screwdriver, 1/4 inch x 142.0 mm
Ratchet screwdriver



EAN	4013288156280	Dimension:	142x37x37 mm
Code:	05051461001	Weight:	186,3 g
Article-No.		Country of origin:	CZ
		Customs tariff no.:	84661038

- Ratcheting screwdriver with Rapidaptor technology for rapid bit change
- Ratchet with fine-pitched toothing for a low return angle
- Switchover (right, fixed, left)
- Maximum torque of up to 50 Newton metres
- Multi-component Kraffform handle for fast and ergonomic screwdriving

High quality bit holder. Includes a ratchet: fine-toothing with a small return angle, switchover (right, fixed, left), maximum torque of up to 50 Newton metres. The Rapidaptor quick-release chuck enables rapid bit change without needing any special tools. The strong permanent magnet holds the bits absolutely securely. Kraffform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Suitable for bits with 1/4 hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173)."