

160 i VDE Insulated screwdriver for slotted screws, 0.8 x 4.0 x 100 mm
VDE Insulated screwdriver for slotted screws



EAN	4013288027252	Dimension:	198x33x33 mm
Code:	05006115001	Weight:	51,4 g
Article-No.		Country of origin:	CZ
		Customs tariff no.:	82054000

- Insulated VDE blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Conical blade, Lasertip

Wera VDE screwdrivers with multi-component Kraftform Plus handle for fast and low-fatigue working: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Individually tested in water bath at 10,000 volts for secure work at the permissible voltage of 1,000 volts. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace. The tips of the Wera Lasertip screwdrivers are microscopically roughened by laser beams. This rough surface literally bites into the head of the screw. Any unintentional slipping out is therefore a thing of the past.