

156-01555

Article Number: 156-01555

Description: Fir Tree Mount Cable Tie, 5.9" Long, .22"-.25" Mounting Hole, 100lb, PAEK, Beige, 500/bag



Base Data	Local Order Number	156-01555
	Type	PAT100RFT6LG
	Color	Beige (BGE)
	Features and benefits	<ul style="list-style-type: none"> <li>• Fir Tree Push Mount offers simple and easy to use method of bundling and fixing cable ties.</li> <li>• The design of the fir tree ensures a positive secure fixing into panels with thicknesses from 1.25 mm to 6.0 mm or threaded blind holes.</li> <li>• The 'disc' on the top of the fir tree covers the hole and minimizes the admission of water and dirt.</li> <li>• High heat resistance allows for maximum performance on both fixing surface and area near bundle.</li> </ul>
	Quantity Per	bag
	Product Description	High heat resistant fir tree and cable tie assemblies, provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.
	Short Description	Fir Tree Mount Cable Tie, 5.9" Long, .22"-.25" Mounting Hole, 100lb, PAEK, Beige, 500/bag
Product Dimensions	Minimum Tensile Strength (Imperial)	100.0lbs
	Minimum Tensile Strength (Metric)	445.0N
	Length L (Imperial)	5.9"
	Length L (Metric)	149.9mm
	Length L2 (Imperial)	0.35"
	Length L3 (imperial)	0.75"
	Length L3 (metric)	19.2mm
	Fixation Method	Fir Tree
	Identification Plate Position	none
	Length L2 (Metric)	9.0mm
	Tie Closure	plastic pawl
	Width W (Imperial)	0.33"

156-01555



Product Dimensions	Width W (Metric)	8.0mm
	Width W3 (Imperial)	0.2"
	Width W3 (Metric)	5.0mm
	Height H (Imperial)	0.75"
	Height H (Metric)	19.2mm
	Height H2 (Imperial)	0.5"
	Height H2 (Metric)	12.6mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.38"
	Bundle Diameter Max. (Metric)	35.0mm
	Disc Diameter (Imperial)	0.73"
	Disc Diameter (Metric)	18.6mm
	Panel Thickness Max. (Imperial)	0.24"
	Panel Thickness Max. (Metric)	6.0mm
	Panel Thickness Min. (Imperial)	0.05"
	Panel Thickness Min. (Metric)	1.25mm
	Mounting Hole Diameter D (Imperial)	0.22 - 0.25"
	Mounting Hole Diameter D (Metric)	5.6 - 6.4 mm
	Mounting Hole Diameter D Min. (Imperial)	0.22"
Mounting Hole Diameter D Max. (Imperial)	0.25"	
Material and Specifications		
	Material	Polyaryletherketone (PAEK)
	Material Shortcut	PAEK
	Flammability	UL 94 V0
	Halogenfree	No
	Operating Temperature	-67°F to +392°F (-55°C to +200°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987