

156-00866



Article Number: 156-00866

Description: Cable Tie and Edge Clip, 50 lb, 8" Long, EC9, Panel Thickness .04"-.12", PA66HS, Black, 500/bag

Base Data	
Local Order Number	156-00866
Type	T50SOSEC9SD
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments. • Two piece assembly allows the mount to slide along the strap ensuring proper orientation. • Cable tie is outside serrated to reduce bundle chafing.
Quantity Per	bag
Product Description	The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.
Short Description	Cable Tie and Edge Clip, 50 lb, 8" Long, EC9, Panel Thickness .04"-.12", PA66HS, Black, 500/bag
Product Dimensions	
Minimum Tensile Strength (Imperial)	50.0lbs
Minimum Tensile Strength (Metric)	225N
Length L (Imperial)	6.0"
Length L (Metric)	150mm
Length L2 (Imperial)	0.6"
Fixation Method	EdgeClip, top, assembled, 2 piece
Identification Plate Position	none
Length L2 (Metric)	15.0mm
Variant	Outside Serrated
Width W (Imperial)	0.18"
Width W (Metric)	4.6mm
Width W2 (Imperial)	0.43"

156-00866



Product Dimensions	Width W2 (Metric)	11.0mm
	Height H (Imperial)	0.05"
	Height H (Metric)	1.3mm
	Height H2 (Imperial)	0.47"
	Height H2 (Metric)	12.0mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.4"
	Bundle Diameter Max. (Metric)	31.0mm
	Panel Thickness Max. (Imperial)	0.12"
	Panel Thickness Max. (Metric)	3.00mm
	Panel Thickness Min. (Imperial)	0.04"
	Panel Thickness Min. (Metric)	1.00mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.3mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HIRHS
	Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	2.152kg