



FEATURES:

- Replaceable tip probe set with sharp stainless steel tip included. (Other tips are available, see model 6475.)
- Designed for most DMM's including Fluke, Wavetek Metorman, Amprobe, and others with safety-sheath banana jack inputs
- Thermoplastic elastomer outer coat provides comfortable grip and flexible strain relief
- Probe and banana plug are molded directly onto the wire for robust pull strength
- Wire is a high strand count silicone wire for extreme flexibility and high temperature resistance
- Banana plug spring is nickel plated Beryllium Copper for long insertion life

MATERIALS:

Probe:

Outer Insulation: Santoprene[®] rubber, color: gray

Inner Insulation: Polypropylene, color: one black, one red

Tip: sharp stainless steel

Wire: 18 AWG

Banana Plug: Nickel plated Brass

Spring – Nickel plated Beryllium Copper

Plug Insulation: Polypropylene, color: one black, one red

RATINGS:

IEC 1010-2-031, Category III 1000V

Operating Voltage: 1000 VRMS

Current: 5 Amperes

ORDERING INFORMATION: Model 6477

Includes a set of one black and one red test lead with two replaceable tips

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA