

Xcelite ErgoCrimp Plus® for 22-10 AWG Non-insulated Terminals Splices

◀◀ previous print close next ▶▶



Product Details

| | |
|------------------------------------|--|
| Catalog No. | ECP101 |
| UPC Code | 037103197146 |
| Crimping Range | 22-10 AWG |
| Connector Type | Non-insulated Terminal/Splices |
| Wire or Cable Size/Type | Solid/Stranded |
| Die Set | D101 |
| Packaging | Industrial Box/Carton |
| Tech. Spec. | <u>Crimping Stripping Tools.pdf</u> |
| Low Res. Image | <u>ECP101_100.jpg</u> |
| High Res. Image | <u>ECP101_300.jpg</u> |
| Operating Ins. | <u>Crimp Tools Instructions.pdf</u> |
| Stock Item | Normal Stock Item |

Package Details (Dimensions)

[Email this Page](#)

Product Features:

- Die set designed for 22-10 AWG non-insulated terminal splices
- Patented ergonomic design makes this tool easy and comfortable to use
- Lowest possible handle forces required
- High quality construction with tight tolerances
- Superior crimp die design insures the highest quality crimp results
- High strength through-hardened alloy steel and precision manufacturing
- Guaranteed for 50,000 cycles
- Precise eccentric adjustment for consistent performance for life of tool
- Tools can be purchased complete with die set or separately
- Special dies are also available upon request