

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0701070008**
Status: **Active**
Overview: SL™ Modular Connectors
Description: SL™ Wire-to-Wire Crimp Housing, Single Row, Version A, without Mounting Ears, 9 Circuits

Documents:

3D Model	Product Specification TS-70541-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-70107-100 (PDF)
Product Specification PS-70400-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>70107</u>
Application	Signal, Wire-to-Wire
Comments	Version A without Mounting Ears
Overview	<u>SL™ Modular Connectors</u>
Product Name	SL™
UPC	800753560833


Physical

Circuits (maximum)	9
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.645/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70107-100
Product Specification	PS-70400-001, TS-70541-001-001
Sales Drawing	SD-70107-0001-0024



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

70107 Series

Mates With

70066 SL™ Crimp Housing A, G and D (Notes: Version C and H will not mate to the 70107 housing series), 70400 SL™ Insulation Displacement Connector Assembly, Version G Housing, 70430 SL™ Single Row Receptacle, Version G

Use With

70021 SL™ Crimp Terminal