

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0561618081**
Status: **Active**
Description: 2.00mm Pitch Crimp Terminal, Female, 22-26 AWG, Gold (Au) Plating, Reel

Documents:

Drawing (PDF)	Application Specification AS-54992-006-001 (PDF)
Product Specification PS-54992-004-001 (PDF)	Packaging Specification 561619200-200 (PDF)
Application Specification AS-54992-005-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	<u>56161</u>
Application	Signal
Crimp Quality Equipment	Yes
Packaging Alternative	<u>56161-8181</u> (Loose)
Product Name	DuraClik™, Mi II™
UPC	800756476667

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	18.300/mg
Packaging Type	Reel
Plating min: Mating (µin)	8
Plating min: Mating (µm)	0.2
Plating min: Termination (µin)	60
Plating min: Termination (µm)	1.5
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A


Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Application Specification	AS-54992-005-001, AS-54992-006-001
Crimp Specification	CS-56161-003-001
Packaging Specification	561619200-200
Product Specification	PS-54992-004-001
Sales Drawing	SD-56161-002



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

56161 Series

Use With

502351 DuraClik™ Wire-to-Board
Receptacle Housing