


Film, Metallized Polypropylene, Safety, F863, 0.22 uF, 10%, 310 V, 110C, Lead Spacing = 15mm



Dimensions

L	18mm +0.3mm
H	13.5mm +0.1mm
T	7.5mm +0.2mm
S	15mm +/-0.4mm
H0	18.5mm +/-0.5mm
F	0.6mm +/-0.05mm

Packaging Specifications

Packaging:	Ammo
Packaging Quantity:	500

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	F863
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL, CQC

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	10%
Voltage AC:	310 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	0.2% 1KHz
Insulation Resistance:	30 GOhms
Max dVdt:	400 V
Safety Class:	X2